







Detector A	V 780/60
BV786	V 780/60
Detector B	V 710/50
BV711 Qdot 700	V 710/50
Detector C	V 660/20
BV650	V 660/20
Detector D	V 610/20
BV605 Qdot 605	V 610/20
Detector E	V 525/50
Alexa Fluor 430 AmCyan BV480 BV510 FVS 510	Pacific Orange Krome Orange V500 V 525/50
Detector F	V 450/50
Alexa Fluor 405 BV421 Cascade Blue CFP Pacific Blue V450	Cerulean DyLight 405 FVD eFluor 450 FVS 450 V 450/50



Detector A	B 710/50
7-AAD PerCP PerCP-Cy5.5 PE-Cy5.5 PI	BB700 B 710/50 FVD eFluor 520 PerCP-eFluor 710 PerCP-Vio700
Detector B	B 530/30
Alexa Fluor 488 FITC GFP BB515 B 530/30 Calcein-AM CFSE	Cy2 DyLight488 FVS 520 Live/Dead Green Oregon Green mClover Venus YFP
Detector C	488/10*
488nm SSC	This auto-selects, and no other parameter can be recorded in this channel



Detector A	Y 780/60
PE-Cy7 PE-Vio770	Y 780/60
Detector B	Y 710/50
PE-Cy5.5	Y 710/50
Detector C	Y 670/30
PE-Cy5 7-AAD (561ex) mPlum	Y 670/14 Y 670/30
Detector D	Y 610/20
PE-CF594 PE-Texas Red Alexa Fluor 568 ECD	mCherry Nile Red PI (561ex) Y 610/20
Detector E	Y 585/15
DsRed PE Alexa Fluor 546 Alexa Fluor 555 Cy3 eFluor 585 NC	mRuby RFP SNARF tdTomato Y 585/42 Y 586/15



Detector A		R 780/60
APC-Cy7 & APC-H7 APC-Vio770	APC-Alexa750 APC-eFluor780	FVS 780 R 780/60
Detector B		R 730/45
Alexa Fluor680 Alexa Fluor700	FVS700 APC-R700	R730/45
Detector C		R 670/14
Alexa Fluor633 Alexa Fluor647 eFluor 660 FVD eFluor 660	APC Cy5 DRAQ5 FVS 660	Live/Dead Far Red R 670/14 R 670/30 TO-PRO-3